



Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours

TEC sesterm 14-inch screen
OEM / ODM.
2 year warranty + work 24 hours



13 Years
Beauty Device Company

2years Warranty



102 Countries

60,000+ Customers



TEC sesterm

1. 808 nm : TEC sesterm 808 nm 3 Alex 755nm 808 nm 1064 nm 1064 nm 1064 nm
2. TEC sesterm 10-1 TEC sesterm : TEC sesterm 10-1 TEC sesterm
3. TEC sesterm 12 TEC sesterm : TEC sesterm 12 TEC sesterm
4. TEC sesterm 24 TEC sesterm : TEC sesterm 24 TEC sesterm
5. TEC sesterm 6.5 TEC sesterm : TEC sesterm 6.5 TEC sesterm
6. CD 7 * 14 TEC sesterm : TEC sesterm 7 * 14 TEC sesterm

Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before



1 Minute
and you're done!

Different spot size Handle color optional



12*20mm



12*35mm



12*20mm



12*35mm

□□□□ □□□□□□

1) 10 .□□□ □□□□□□ 40-10 □ □□□□ 16 / □□□□ 12 / □□□□

.□□ □□□□ □□□□ □□□ □□ □□□□ □□□ □□□□ 38 * 12 / □□□ □□□□ 20 * 12 □□□□ □□□ (2

.□□□□ □□□□□□ □□□□ □□ □□ □□□□□ □□□□□ □ □□□□ □□□□□□ □□□ □□□□ □□□□□□□□ (3


□□□ □□□□ □□□□□ □□□□ □□□ □□ □□□□ □ □□□□□ □□ □□□□ □□□ □□□□ □□□□□□□□□□ (4.

808 Hair Removal treatment pictures



□□□□

755 □□□□ 3 □□□□nm 808nm 1064nm □□□□ □□ □ □□□□ □□□ □□□□□ □□□□□ □ □□□ □□ □□□□□ □□.


	755 nm for white skin (fine, golden hair removal);
	808nm for yellow neutral skin (brown hair removal);
	1064nm for black skin (black hair removal)



A natural



B energy absorbed by hair




C hair follicle died

Treatment effect



Hair in the treatment area can be easily pulled out



Before




After



Before



After



Before



After

Before



After



□□□□□ □□□□□□

1. □□□ □□□□□□ □□□ □□□□□ □ □□□□□ 14 □□□□ □□□□ □□□□□ □□□□□
- .□□□□□ □□□□ □□□□ □□□ 6 □ □□□ □□□□□ □ □□□□□ / □□□ .2
- .□□□ □□□□□ □□□□ □□□□□□□□□ .3
- / □□□□) □□□□□□ □□□ □□□□□□□ □□□□□□ .4...)



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,



1. 明光科技 mingliangkj:

明光科技 是一家专业从事 包装 及 物流 服务的 企业。 我们 拥有 13 年 的 经验。

Service users all over the world



.□□□□ □□□ □□ □□□ □□□□□□ □□□□□ □□□ <<

 $\square\square\square\square \square\square\square\square\square\square \square\square\square \square\square\square \square\square\square <<.$

>> LOGO □□□□ □□□ □□□□□□ □□□□ □ □□□□ □□□ □□ □□ □□□.

Custom Section

CASE design



LOGO design



SYSTEM design




3. 1. 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



4. 認證證書 認證證書 認證證書

