



אנחנו מציעים לך את הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך

1. הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון של 15 שניות בלבד.
2. הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר.
3. הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר.
4. הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר 1064 ננומטרים 808 ננומטרים 755 ננומטרים .הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר.
5. הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר 50 ננומטרים .הפתרון הטוב ביותר להיפרדות מהשיערות העודפות שלך הוא הפתרון הטוב ביותר.

[למידע נוסף](#)

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



- >>> Big 20*12 □□□□ □□□□□□mm, 12*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment
>>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



مورد	755nm/808nm/1064nm لیزر دایود عمودی
نوع لیزری	نوار لیزر پزشکی لیزر دایود: 10 بار / 15 بار
قدرت هر نوار	120w/بار پزشکی
سیستم نمایش	صفحه نمایش لمسی 14 اینچی رنگی واقعی
طول موج	808nm/755nm/1064nm
Spot Size	24*12mm ² پزشکی یا 12*36mm ²
طول عمر دسته لیزری	حداقل 40 میلیون شات
انرژی	(اختیاری cm2/قابل تنظیم) تا 150 J / cm2 -10
مدت زمان نبض	30 ~ 400 میلی ثانیه قابل تنظیم
فرکانس	هرتز؛ 1.0-10
سیستم خنک کننده	کمپرسور هوا گردش آب را بندید
قدرت دسته	1000w/1200w/1600w/1800w
قدرت ماشین	4000 وات
منبع برق	ولت / 50 هرتز یا 110 ولت / 60 هرتز 220
دمای کریستال	تا 3 درجه سانتی گراد -20
دمای ماشین	درجه سانتی گراد 24
نیروی مورد نیاز	AC220V/110V 50~60Hz



OEM و ODM خدمات:

- طراحی و تولید

- تامین قطعات و مواد اولیه

- کنترل کیفیت و تست نهایی

- بسته بندی و ارسال به مشتریان

- خدمات پس از فروش و تعمیرات

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



Our factory is equipped with advanced manufacturing equipment and a highly skilled workforce, ensuring the highest quality and precision in every product we produce.

Contact us today at 1064 808 755 for more information.

• 24-hour customer support and technical assistance.