



Picosecond laser

picosencond

>> Instantaneous blasting

>> Imported stone

>> Q.

>>



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
755nm



Fixed
532nm




Fixed
1064nm



.000 00 00000 000 0000 7 00 1 00 00 0000 000000 00 00

1320/□□□□□□ 532/□□□□□□ 1064 □□□□□□ □□□□ □□□□□□ 532/□□□□□□ 1064
□□□□ □□□□□□ 755/□□□□□□.

Working Principle



* 1064/532 nm 照射 照射後 照射前 照射後 照射前 照射後 照射前 照射後 照射前 Nevus of Ota 照射 照射.

* 1320 nm 光源 照射 した 場合 の 透過 率 測定 結果 (透過 率 100%)

* 755 nm 光源 照射 による 光 吸収 測定 結果

□ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □

* 1064/532 000 0000 7-1 0000 000000 000000 000000 0000 000000 0000 000000 0000 00000000
000 000000 0000.



Professional Screen, Easy operation



8.4 本公司 代理 各种 进口 激光 美容 仪器 设备 价格 优惠 质量 保证 售后服务 周到 欢迎 咨询
 6 本公司 代理 各种 进口 激光 美容 仪器 设备 价格 优惠 质量 保证 售后服务 周到 欢迎 咨询
 本公司 OEM 各种 进口 激光 美容 仪器 设备 价格 优惠 质量 保证 售后服务 周到 欢迎 咨询

1064nm 532nm

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm &1320nm &1064nm(Adjustable)&532nm(Adjustable)
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful
aluminum alloy case



N.W 20KG



G.W 30KG



15 Years Laser Beauty Device Manufacturer

- High Feedback
Top10 Supplier
- OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2 1000 1000 100 1000000 10000 10 10000000 1 10000 10000 10 1000 10000 10 1000000 1000



Custom Services

Customized service to meet your needs




CUSTOM SCREEN



MACHINE COLORS



MACHINE SYSTEM



TROLLEY ALUMINUM BOX



PHONE HOLDER