



TEC laser hair removal machine is the best choice for your salon. It is faster, stronger, and smarter than other machines. It can remove hair in 24 minutes. It is the best choice for your salon. It is faster, stronger, and smarter than other machines. It can remove hair in 24 minutes.



- 1) 10. TEC laser hair removal machine 40-10 TEC laser hair removal machine 16 / TEC laser hair removal machine 12 / TEC laser hair removal machine
- 2) TEC laser hair removal machine 36 * 12 / TEC laser hair removal machine 24 * 12 TEC laser hair removal machine (2)
- 3) TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine (3)
- 4) TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine
- 5) TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine TEC laser hair removal machine

1 minute
and you're done

35mm {

FASTER

1. .

2. .

3. .

4. OEM (

7558081064

16 12 10 8

755 808 1064 808

0-150J/cm2

1-10

40-800

14.0 TFT True Color LCD

4000

220 60 / 110 50 /

62 78 /

N.W/G.W

62 78 /

[illegible]

Company Strength

The collage consists of four images arranged in a 2x2 grid, each with an icon and text overlay:

- Top Left:** A person working on a computer with a circuit board on the desk. Icon: Two people. Text: **50+** R&D team.
- Top Right:** Three people working together at a table. Icon: Two hands shaking. Text: **500+** Cooperation Case.
- Bottom Left:** A person working on a machine in a factory. Icon: A calendar. Text: **17 Days** Product deadline.
- Bottom Right:** A row of medical ultrasound machines. Icon: A globe. Text: **100+** Export country.

- >>OEM your own machine body.
>>OEM your own program software.
>>OEM pretty machine colors.
>>Print your LOGO on machine body and screen.

Custom Section


CASE dedign



LOGO design



SYSTEM design



□□□□ □□□□



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

