

Two major service guarantees
Worry-free after-sales

24 hours offers the solution
Solve problems quickly with your active cooperation

Warranty period, Send your replacement parts for free

□□□□ □□□□ □□□□ □ □□□□□ □□□□ □□□□□ □□□□ □□ □□□□□□ □□ □□ □□□□ □□ □□.

A handheld, black and silver device, likely a portable X-ray or radiation detector, shown against a dark background. The device has a black handle and a silver-colored head. The head features a small, rectangular display screen showing some text and a blue bar. Below the screen, there is a small, dark, circular component, possibly a lens or a sensor. The device is shown from a side profile, angled slightly upwards.


□ □ □ □ □ □

.0000 0000 0000 0000 00 0000 0000 3 00 000 0000 000000 40 00 000 *

□□ □□□□ □□□□ □□□ 1600 / □□□ 1200 □□□□ □□□□ : □□□□ □□□□ *

製品は、標準的な環境で動作することを保証します。 * Dual-TECは、製品が動作する環境温度を調整するための機能です。

□□□ □□□□□□ 40 :□□□□□□ □□□ *



808 V19

1600 1200

38*12 20*12

* 350

* () *



* () *

* () *

* 808nm 808nm 808nm 808nm 808nm

Has a wide range of applications



+



+



+



755NM
Sebaceous Gland

808NM
Bulge


940NM
Skin rejuvenation

1064NM
Hair Bulb

1. Alex 755nm 808nm 808nm 808nm

2. 808nm 808nm 808nm 808nm 808nm

3. 1064nm 1064nm 1064nm 1064nm 1064nm



□□□□□□ □□□

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

□□□□□ □□□□□□□ □□□□□ □□□□ □□□□□

1. □□□□ □□□ □□□□□□□ 14 □□□□ □□□□□ □□□□

□□□□ □□□ 6 □□□□ □□□□ 6 □□□ □ □□□ □□□□□□□ □□□□□ □□□□ □□□□ .2

□□□ □□□□□ □□□□□ □□ □□□ □□□□□ □□□□ □□□□□ □□□□□ 6 .3

□□□□□□□ □□□□□□□ .4 OEM (□□□□□□□/□□□□□□□...)

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen

>>R & D team and Quality inspection Show

6. □□□□□ □□□□□

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE

Obtained multi-way authoritative certification,
product testing certification, product patent authority,

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE

Obtained multi-way authoritative certification,
product testing certification, product patent authority,

0000000 0 0000000 0000000 00 000000 0 0000000 0000 0000 0000000 0 0000000 0000000.
 0000000 00000000 0000 0 0000 00000000 0 0000 0000000 000000 000000 00.000000000000 0000000 00.
 0000 00000 0000000000000 000000 0000000 00 0000000000 00 0000 0000 00000 00 0000000 00 00 000000 00 000000
 0000000 00000000.