

NEW ! Technology



W مزیت دستگاه لیزر موهای زائد دیود تیتانیوم 1600

1. نانومتر از سیستم حذف موهای زائد لیزر دایود استفاده می کند، مناسب برای انواع پوست از بین بردن موهای 1064 808 755 راند.

2. میله های لیزر طلایی از آلمان یا ایالات متحده وارداتی، حداکثر 40000000 طول عمر بیشتر

اطمینان حاصل کنید که لیزر به طور مداوم بدون تهویه مطبوع در تابستان کار می کند، 3. WTEC. سیستم خنک کننده 1600

4. بدون اسکار، بدون هیچ گونه عارضه جانبی.

5. قدرت بالا، بدون درد، 3-5 جلسه حذف دائمی موهای زائد

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



12*20mm or **12*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

12*20mm {




12*35mm {



□□ □□□□ 1 □□□□ !!!


**NEW !
Technology**




**High-quality
laser bars
imported from
USA**

1000/1200/1600ww high power



Fast hair removal



⌚ 10bar
1000W




⌚ 12bar
1200W



⌚ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm

The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin



در 1 سیستم، 24 ساعت توانایی کار 3 TEC سیستم خنک کننده 3 در 1: خنک کننده هوا خنک کننده ابی خنک کننده میلی متر / 12 * 35 میلی متر اندازه نقطه بزرگ، کاهش زمان درمان برای 1/5 اصلی 20 * 12



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{ cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



اینج صفحه نمایش لمس واقعی، تجربه لمس فوق العاده خنک را ارائه می دهد. 14 / 12.4 *

پذیرفته شده است. تنظیم پارامتر درست است. OEM * سرویس

* لوگو و زبان خود را به صورت رایگان اضافه کنید

The new 14-inch screen is clear easy to operate.



OEM/ODM SEVRICE

مشخصات از دستگاه لیزر موهای زائد تیتانیوم 1600 وات دایود

مورد	755nm808nm1064nmلیزر دایود عمودی
نوع لیزری	لیزر دایود، 10 بار 12 بار / 16 بار
قدرت هر نوار	100w/bar
سیستم نمایش	صفحه نمایش لمسی رنگی واقعی 12.4/14 اینچی
طول موج	808nm/755nm/1064nm
اندازه نقطه	میلی متر مربع / 12 * 35 میلی متر مربع 20 * 12
طول عمر دسته لیزری	حداقل 20-40 میلیون شات