



Household A1

Three bands: 755nm/808nm/1064nm

Suitable for all skin tones

Laser painless hair removal

1. The device is a laser hair removal device.

2) The device is a laser hair removal device.

3) The device is a laser hair removal device.

4) The device is a laser hair removal device.

5) The device is a laser hair removal device.

Machine Parts



Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

重量 600g 長さ 5cm 幅 14 * 14cm 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 1064 冷却効果 808 冷却効果 755 冷却効果 冷却効果

2) 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果 冷却効果.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13.3 inch 4K true color touch screen
2. 6 language for your choice. Super cool touch Experience .
3. Special language can be added according to your actual requirements.
4. OEM (logo/brand...)

We have OEM Services

Serving your needs



--	--	--	--	--	--	--

Weifang Sunshinekj electronics Co., Ltd (股票代码:MLKJ) 公告称 自 2019 年 10 月 14 日起 公司 股票 停牌 14 个交易日.

13 Years Laser Beauty Device Manufacturer

- High Feedback
Top10 Supplier
- OEM & ODM
SERVICE



13 Years Laser Beauty Device Manufacturer



• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. 13 Years Laser Beauty Device Manufacturer
High Feedback Top10 Supplier
OEM & ODM SERVICE
Premium OEM Factories
High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



□□□□ □□□□ □□□□

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service