



1.3 1000 1000 1000 1000 1 1000 3 755 808 1064 1000 1000 1000
 1000 1000 :1000W/1200W/1600W 1000 1000
 !1000 1000 1000 35*12 1000 1000 20*12 1000 1000 1000 1000 1000 .2
 1000 1000 1000 1000 1000 :1000 1000 1000 .3 Dual-TEC 1000 1000 1000
 .1000 1000 1000 1000 24 1000 1000 1000 1000 1000
 1000 1000 1000 1000 1000 :1000 1000.4

1000 1000 1000 1000 1000:





Different spot size Handle color optional



□□□□ □□□□ □□□□ □□ □□□□ □□□□□□□□

□□□□ □□□□ □□□□ □□□□□□□□ 755 □□□□

Speed Diode 808nm □□□□ □□□□ □□□□

Long Pulse 1064nm □□ □□□□ □□□□ □□□□ □□□□

Treatment effect



□□□□□□ □□□ □□□□□□□□

1. 0000 000 6 0000 0000 6 000 0 000 00000 000000 00000 000
000 00000 00000 00 000 00000 0000 00000 00000 6 .2
000000 00000 .3 OEM 00000/0000) 00000 00...)

