



808 Diode Laser

Big Power: 1000w 1200w 1600w

Triple wavelength: 755nm 808nm 1064nm

For different skin type: white, brown, black

□□□□□□ □□□□□□

Machine Parts



□□□□ □□
□□□□ □□


□□□□ □□□□ □□ □□□□ □□□□ □□□□ □□□□
755 □□□□□□ 1064/□□□□□□ 808/□□□□□□

6	8
800w/1000w/1200w/1600w	16 / 12 / 10 /
10.4	40
10~150 j/cm2	10 ~ 300
1	2500
-29 ~ 5	



1. TEC
 2. 1600 800 16 8
 3. 10-1 35 * 12 / 20 * 12 /
 4. TEC

Laser show Handle laser bar optional



808nm : 808nm
 755nm : 755nm
 ND YAG 1064nm: 1064nm

Before and After

Treatment comparison



Product Display



□□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□!