

□□□□□□

*.□□□ □□□□ □□ □□□□□ □□□□ □□□□□ □□ □□□□□□

.□□□□ □□□□ □□□□ □□ □□□□□ □□□ 3 □□ □□□ □□□□□□ 40 □□ □□□ *

□□□ □□□□□□ □□□□ □□□□ □□□ □□□ 1 □□ 3 □□□□□□□□ 755 □□□□□□□□ 808 □□□□□□□□ 1064 □□□ 3 *

□□ □□□□□ □□□□ □□□ 1600 / □□□ 1200 / □□□ 1000 □□□□ □□□□ :□□□□ □□□□ *

□ □□□□ □□□□ □□□ □□□□□ □□□□ □□□□ 36*12 □□□□ □□□□ 24*12 □□□□□ □□□□ □□□ □□□□□□ *

!□□□

□□□ □□ □□□□□ □□□□□ □□□ □□□□□ :□□□□□ □□□ □□□□□ * Dual-TEC□ □□□ □□ □□□□□□□ □□□□ □□□□□□□□

.□□□□ □□□□ □□□□ □□□□ 24 □□□□ □□□ □□□□ □□ □□□□□□

□□□ □□□□□□□ 40 :□□□□□□□ □□□ *

350g lightweight **handle**, more ergonomic

Available in **black or white**



□□□□ □□□□□□□□

□□□□□□ □□□□□□ □□□□ □□□ 1800 □□□□ 1200 □□□□ □□□□

□□□ □□□□ 36*12 □□ 24*12 □□□ □□□□□□□

* 350 □□□□□□ □□□□□□ □□□□ □□□□ □□□□ □□□ □□□□□ □□□□ □□□ □□□

□□□□□□□ □□□□ □□□□ □□ □(□□□□□ □ □□□□□□□ □□□) □□□ □□□□□ □□□□ □□□□ □□□□□□□□ □□□□ □□ *

□□□□



1. 1200W TEC Cooling system

- * 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle
- * 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle
- * 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle 1200W TEC Cooling system 12*24mm handle

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas
like face, arms, armpits, chest, back, bikini, legs...



2. 1200W TEC Cooling system 12*24mm handle

1. Alex 755nm 1200W TEC Cooling system 12*24mm handle

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. 14 days before and after treatment

1. 14 days before and after treatment
2. 6 days before and after treatment
3. 6 days before and after treatment
4. OEM (OEM/ODM...)

5. OEM / ODM

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

6. OEM / ODM

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs



CERTIFICATE


Obtained multi-way authoritative certification,
product testing certification, product patent authority,



Our products are certified by the FDA, CE, and other international organizations. We have obtained multi-way authoritative certification, product testing certification, product patent authority, and other certifications. We have a strong R&D team and a complete production system. We can provide OEM/ODM services for our customers. We have a good reputation in the market and a wide range of customers. We will continue to improve our products and services to meet the needs of our customers.

SHIPPING

Welcome to visit our factory



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month