





TEC 24 10 16 / 12 / 35 \* 12 / 20 \* 12 (2) (3) (4) (5) 350

- 1) 10 . 40-10 16 / 12 /
- . 35 \* 12 / 20 \* 12 (2)
- (3).
- 4) .
- 5) 350 .

1 minute  
and you're done

35mm {

FASTER

1. .

2. .

3. .

4. OEM (

16 12 10 8

755 808 1064 808

0-150J/cm<sup>2</sup>

1-10

40-800

LCD 14.0 TFT True Color LCD

4000

220 60 / 110 50 /

N.W/G.W 62 78 /


# Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

## Custom Section


### CASE design



### LOGO design



### SYSTEM design




□□□□ □□□□

# CERTIFICATE DISPLAY



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,