



Avantages

1. Prise de poignée rotative, plus facile à installer.
2. Tube résistant à l'usure, plus durable. La poignée est moulée par injection, plus légère et plus pratique.
3. Le tout nouvel écran de 12,4 pouces est clair et facile à utiliser.
4. La poignée est moulée par injection, plus légère et plus pratique.
5. Améliorez le trou de dissipation thermique, l'effet de dissipation thermique est bon et la dissipation thermique est plus rapide!




- * Taille du spot 12*20mm, 12*35mm, pour l'option
- * Poignée de 450 g, poids léger, traitement de glissement rapide gratuit
- * Avec voyant lumineux, pour montrer l'état de fonctionnement (sur la machine et la poignée), sans encombre utiliser
- * peut être sélectionné Paramètres pour différents tons de peau

THE POWER OF THREE

A white laser handpiece with a yellow tip, shown from a side profile.

“ The revolutionary Soprano Platinum Trio handpiece offers coverage and efficacy levels that have never before been achieved. Having the three most effective wavelengths operating simultaneously is groundbreaking for the laser hair removal industry. ”



7558081064nm

Les 3 vagues fonctionnent dans le même manche en même temps :

755nm pour les peaux blanches (cheveux fins et dorés)

808nm pour peau jaune/neutre

1064nm pour les noirs (cheveux noirs)

Comparaison des effets

Treatment effect

Suitable to any color of skin



Before&After



Écran d'affichage



Filtrer

1. Grand écran de 12,4 pouces, touche rapide
2. Homme et femme, 6 parties du corps, 6 types de peau définissant un logiciel intelligent
3. 6 options de langue, votre langue maternelle peut être ajoutée
4. Service de programme OEM gratuit (logo/système...)



Notre usine est le fabricant professionnel de machines de beauté depuis plus de 14 ans. Nous nous concentrons sur une bonne qualité et un bon service, vous soutenons, vous et votre entreprise!

Certificate display

Certificate is the best guarantee for you



Emballage et expédition

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,