

NEW PRODUCT

*D10*

## Portable Hair Removal Machine

-Convenient and efficient hair removal-



**Machine d'épilation permanente au laser à diode d'épilation au laser  
Allemagne 755 808 1064 diode laser diode ipl épilation au laser**

# Product details

Ultra-thin large screen, cool light strip



## Avantages

- \* Barre laser importée des États-Unis ou de l'Allemagne 10bars/15bars
- \* Plus de 50 millions de prises de vue, plus de 3 ans n'ont pas besoin de changer de nouvelle poignée.
- \* 3 vagues 1064nm 808nm 755nm, 3 en 1 tous les types de peau peuvent être utilisés



# Working Principle

Suits for all skin and hair types



**12\*20nm**

755nm Laser  
808nm Laser  
1064nm Laser



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

## Description des produits

## Mini Portable

The net weight of the handle is  
about equal to one iphone

**285g**

Ergonomic handle  
It's not tiring to take off



### À propos de la poignée

Grande puissance 1200 W/1800 W pour le libre choix

Taille de spot 12\*24 ou 12\*36mm

\* Poignée médicale de 285 g, poids léger, traitement de glissement rapide gratuit

\* Avec voyant, pour montrer l'état de fonctionnement (sur la machine et la poignée), utilisez en toute sécurité

**1 minute de glaçage rapide, expérience de traitement confortable et indolore**

# What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,  
the handle can quickly frost.





800/1000/1200/1600W

**50 Million Shots**

**USA / Germany Imported Laser Bar**

**755nm+808nm+1064nm**



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)





**YAG 1064nm**

**For black skin**

(black hair removal)

**7558081064nm, adapté à l'épilation permanente de tous les types de peau**



## Product parameters



Device Name	Diode Laser Machine
Model Number	Diode Laser D10
Wavelength	755+808+1064nm Technology
Screen size	12inch 4K-HD screen
Lifetime	50 Million shots
Pulse Duration	10-300ms
Laser Bar	100w for each one America Coherent Laser Bar
Frequency	1-10hz
Spot size	12x20mm Spot Size
Energy	1-150J
Cooling System	TEC cooling circulation
Power Of Machine	2500W
Voltage	AC220V 50HZ/60HZ
Demension of machine	380mm*460mm*300mm
Package	Aluminum box
Warranty	2 years for machine 1 year for handle

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

**Service en ligne 7 \* 24 heures!**  
**Bienvenue à consulter!**