



Machine d'épilation ménagère portable Avantages

- 1) Montrez que le volume global de la machine est très faible.
- 2) La poignée d'affichage est petite, la poignée 168g est très légère
- 3) La machine est un compresseur avec une efficacité de réfrigération élevée et un faible bruit
- 4) La machine est légère et facile à transporter

Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

Mini poignée laser à diode, taille de tache 14 * 14mm, 5 bars 600W

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) Laser diode 755nm 808nm 1064nm, épilation pour tous les types de peau

2) Refroidissement à l'eau refroidissement d'air refroidissement de compresseur, pour une épilation sans douleur.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13,3 pouces écran tactile, humanisé conçu
2. Mâle / femelle, parties du corps, 6 types de peau pour option.
3. Anglais votre langue maternelle.
4. Service de programme OEM gratuit (logo / système...)

We have OEM Services

Serving your needs



Notre usine

Weifang Sunshinekj Electronics Co., Ltd (abréviation: MLKJ) est un fabricant de matériel de beauté hautement professionnel et expérimenté en Chine, a 14 ans dans l'industrie de la beauté

13 Years Laser Beauty Device Manufacturer

- High Feedback
Top10 Supplier
- **OEM & ODM
SERVICE**



13 Years Laser Beauty Device
Manufacturer

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE



Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. Nous avons une production professionnelle R & D Departments, peut fournir un support technique, une garantie de 2 ans



L\emballage du produit

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service