

Épilation professionnelle au laser à diode 808nm Machine d'épilation au laser à diode 808

* Adapté à [tous types d'épilation](#).

* [Permanent](#) épilation.

.

2 YEARS WARRANTY

Smart clinic data center

- Large 12*35 spot size for quick treatment
- TEC continuous cooling system
- Single/Two connectors
- Smart clinic data center
- User friendly large screen
- I-VI skin tones and tanned skin

Most important thing

3 combined wavelengths covering the optimal treatment

Painless Proven safety Permanent hair removal . All skin types, even tanned skin



Les avantages de Épilation au laser à diode 808nm

1) Convient pour **épilation toutes zones** tels que : visage, bras, aisselles, poitrine, dos, bikini, jambes...

2) **Traitement rapide**, fréquence 1-10hz.

3) Convient à tous les types de peau et de cheveux



Poignée d'épilation au laser à diode 808nm

* Barre importée des États-Unis, énergie plus stable et plus forte.


* Longue durée de vie, coups jusqu'à 40 millions, sans entretien.

* Taille du spot : 10*20mm / 12*35mm * Refroidissement par la glace, les clients ne ressentent aucune douleur, traitement d'épilation confortable.

* Forte puissance, 12 bar 1200W, épilation rapide. 10 bars 1000W, 16 bars 1600W également disponibles

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

Before



After



Treatment effect



Hair in the treatment area can be easily pulled out



Before




After




Before



After



Before



After

*12,4 pouces grand écran intelligent

* Plusieurs langues disponibles, votre propre langue peut être ajoutée.

* Salon, clinique, tout ce que vous voulez logo peut être ajouté.