

# Diode Laser



15 Bar **1800W** Handle

\*Increase the treatment head of nasal hair  
and treat small parts easily



## Popular models

### Advantage of 755 808 1064nm laser diode hair laser removal

1. 755 808 1064 nm from Alma Technology .
2. For all skin and hair style removal .
3. Effective for the hair follicles produce heat accumulation, Permanent Painless hair removal.
4. Almost no skin scattering, no harm to the skin and sweat glands, no scar, no any side-effect
5. 3 in 1 cooling system: Air Cooling + Water Cooling +TEC Cooling 3 in 1 System .24 hours working ability
6. 12\*35mm Big Spot Size ,Reduce treatment time for original 1/5
7. Add Logo and language for free .



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...  
It also have the skin renewing and skin tightening at the same time.



### Product Description



**Handle Details:**

- 1)Diode laser hair removal is painless
- 2)Safe permanent hair removal on all skin types
- 3) Frozen ice cooling sapphire crystal, for painless hair removal.

**Painless, ice-comfortable treatment process**



- 1) Use Italy imported high pressure pump, 40,000,000 longer lifespan
- 2) 2 Filters, 1 filter for soften water, 1 filter for impurity separate.
- 3) High powe,strong energy, get good hair removal effect.



New handle design

755 808 1064 nm from Alma Technology

Spot size 12\*20mm, 10 bars 1000w or 12bars 1200w

Spot size 12\*35mm, 16 bars 1600w.

Suits for all skin and hair types treatment.

