

Diode Laser

ice Hair removal



1200W + 1800W Sopran Titanium hair removal machine

1. Laser technical, suits for all skin and hair types.
2. Handles: Spot size 12*24mm, the other 12*36mm
3. Fast treatment: 1-10Hz frequency, Germany imported laser bars.

Products Description

Air + water + compressor refrigeration
Ice sensation treatment, comfortable and painless



Super cooling effect, the handle temperature can be reduced to -25 °C

Handle of Soprano Titanium hair removal machine

1.12*24mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12*36mm can use at large parts of the body, such as back, arms and legs.....

Triple wavelength included:755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

Medical 1200W/1800W

50 Million Shots

USA / Germany Imported Laser Bar



755nm+808nm+1064nm



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)

10bars 1200W+15bars 1800W diode laser:

* Germany Dilas imported laser bar. (Newest and Best Quality Golden Laser Bar)

* Shots: 20-50 million shots time

* 755 808 1064nm is for all skin and hair style hair removal



Screen Display

- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option, easy to operate.
- 3) OEM service: your logo can be added on machine screen for free, accept your special language.