

**HIGH POWER  
DIODE LASER**

755+808+1064nm  
For all skin and hair types

Newest!

[Learn more details](#)

### Advantages

- \* USA or Germany imported laser bar 8—16bar.
- \* More than 50 million shots , more than 3 years don't need to change new handle.
- \* 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used





**Arm** hair removal



**Lip** hair removal



**Face** hair removal



**Leg** hair removal



**Back** hair removal



**Underarm** hair removal



**Bikini** hair removal



## **DIODE LASER**

755/808/1064nm diode laser, for all type skin hair removal, painless



### **ADVANTAGE**

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



### **About Handle**

1200w ,1800w big power for free choice  
12\*20 or 12\*35mm spot size

\*350g Medical handle, light weight, free quick slide treatment

\* With indicator light, to show working condition(on machine & handle), safely use



800/1000/1200/1600W  
**50 Million Shots**  
USA / Germany Imported Laser Bar

755nm+808nm+1064nm



**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)

# • *Cooling effect* •

The handle is frosted for one minute,  
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.





✓ 14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA imported, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



Model	808V30
Laser Type	Germany/USA imported, 8----16 bars, 800W----1600W
Display	14 inch 4K touchable screen
Wavelength	808nm or 755nm 808nm 1064nm
shots	50 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*20mm or 12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg



# Premium OEM Factories

High-performance manufacturing capacity  
R&D capability for customization  
Professional certifications and approvals



For more model details, please contact us!  
Online 24 hours!!