



## DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

[MORE](#)

### **Why all the beauty salons & beauticians choice titanium**

1. Professional. we have more than 15 years experiences in the High-end beauty machine area.
2. Safety. no side effect on skin and sweat glands, no scar.
3. Fast cooling, which achieve painless hair removal.
4. Popular. Triple wavelength: 755nm+ 808nm+1064nm ,suitable for all the skin types, black skin fine hair all can be easily removed.
5. High energy. Lager spot size, 50 million shots, effectively destroy hair follicles, permanent hair removal.

### **Handle show**

# 12\*24mm or 12\*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



- >>> Big spot size 12\*20mm, 12\*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment  
>>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm  
**For white skin**  
(fine, golden hair removal )



SPEED 810nm  
**For yellow neutral skin**  
(brown hair removal)



YAG 1064nm  
**For black skin**  
(black hair removal)



## Treatment Effect

This is the clinical result of hair removal  
It takes 3--5 times to realize  
permanently hair removal



# New upgrade system

The newscreen is clear easy to operate.



- \* 4K 14 inch Screen, offering super cool touching experience.
- \* OEM service is accepted. adjusting parameter is ok.
- \* Add your logo and language for free

## Specification of Diode Laser Hair Removal Machine

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser medical laser bar :10bars/15bars
Power of each bar	Medical with 120w/Bar
Display system	14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	Medical with 12*24mm²/12*36mm²
Laser handle lifespan	At least 40 million shots
Energy	10-150 J / cm2 adjustable (up to 150J/cm2 optional)
Pulse Duration	30~400ms adjustable
Frequency	1.0-10 Hz;
Cooling system	Compressor+air+close water circulation
Handle Power	1000w/1200w/1600w/1800w
Machine Power	4000w
Electrical source	220V/50HZ or 110V/60HZ
Crystal temperature	-20~3°C
Machine temperature	24°C
Power requirement	AC220V/110V 50~60Hz



**15 Years**  
Laser Beauty Device  
**Manufacturer**

## Our Showroom



**Professional OEM ,ODM Services:**



- Print any color .
- Add your logo
- Add any language into machine system.
- Design exclusive machine shell for you , form your own brand in market .
- Design new interface and system of machine , make it most convenient to you and your clients

# Production Process



Warehouse spare parts



Parts assembly



Precision machining



Handle fabrication



Product assembly process



Quality inspection  
of finished products



Product packaging

**Please consult us for more details.  
24 hours online!**