



Diode laser hair removal machine.

- * No pigmentation. Suitable for any kind of skin;
- * Suitable for any kind of skin ;
- * Safe and Fast.
- * International Hair Removal Golden Standard;
- * The optimal laser wavelength 808nm or 755+808+1064nm;

350g
Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle


1200W diode laser hair removal

Three Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison





Characteristic selling point

1. Brand new 15.6 inch screen is clear and easy to operate.
2. Handle is injection molding design, lighter and more practical.
3. 3D LOGO with luxurious texture.
4. Rotable handle plug, easier to install.
5. Wear-resistant tube, more durable.
6. Two handle racks, more convenient in operation.

If you need help to know more, welcome to consult!