

## Advantages

\*.3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used

High power: NEW 1000W/ 1200W /1600W handle for options

\*.handle spot size 12\*20mm, 12\*35mm, face & body hair removal solution!

\*.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time. \*.Long life: 40 million shots

\*.Three wavelengh diode laser.

\*.Golden laser bars from German or USA imporved 40,000,000+ longer lifespan.


\*.Safe, Fast, Painless permanent

\*.For all skin and hair style hair removal

\*.14.0 inch true color touch screen with 6 skin colors.

## What is diode laser hair removal?


Alma soprano xl titanium Diode laser hair removal comes with 808nm wavelength laser stack or 755+808+1064 triple wavelength laser stack with semiconductors technology. They are assembled together to produce light for permanent hair removal/hair reduction/depilation/epilation treatment!



Emit a laser beam



The laser beam is absorbed by hair follicle melanin




Different color hair has different ability to absorb light wave



After absorption, the laser energy will be converted into heat energy



Hair follicles and surrounding stem cells lose their activity and fall off



So reach hair removal effect



755+808+1064nm Platinum Style Technology.

The 3 waves works in the same handle at the same time:

755nm for white skin( fine, golden hair)

808nm for yellow/neutral skin


1064nm for black(black hair)

## Treatment effect

### Stuit to any color of skin



### Before&After



Real Display Of Treatment Effects: Real painless and permanent hair removal , with obvious results.

We promise that your clients and you will be satisfied with our quality and treatment effects absolutely

## BEFORE AND AFTER TREATMENT

MAKE YOUR SKIN SILKY AND FULL OF CHARM!

