

**HIGH POWER
DIODE LASER**

755+808+1064nm
For all skin and hair types

Newest!

[Learn more details](#)

Advantages

- * USA or Germany imported laser bar 8—16bar.
- * More than 50 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used





Arm hair removal



Lip hair removal



Face hair removal



Leg hair removal



Back hair removal



Underarm hair removal



Bikini hair removal



DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



About Handle

1200w ,1800w big power for free choice
12*20 or 12*35mm spot size

*350g Medical handle, light weight, free quick slide treatment

* With indicator light, to show working condition(on machine & handle), safely use



800/1000/1200/1600W
50 Million Shots
USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



✓ 14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA imported, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



Model	808V30
Laser Type	Germany/USA imported, 8----16 bars, 800W----1600W
Display	14 inch 4K touchable screen
Wavelength	808nm or 755nm 808nm 1064nm
shots	50 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*20mm or 12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



For more model details, please contact us!
Online 24 hours!!