

360° bidirectional rotation

Rotating the machine without moving
Efficient and labor-saving



--Application of laser hair removal machine

- * High power diode laser with nice cooling technology, for hair removal with painless!
- * Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...
- * Frequency 1-10hz. treatment fastly!!!

Machine for fast and permanent hair removal . Painless!!



The handle can be placed **at will**



Do as one wishes

Exfu NEW ARRIVAL

Style: Stationary



7
93
26.0
600
READY

Suitable for any unwanted hair on areas like face, arms, armpits, back, legs, bikini, chest...

Triple wavelength included:755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

350g lightweight handle, more ergonomic

Available in **black or white**

			
spot size:12*36	spot size:12*24	spot size:12*36	spot size:12*24

Suitable for any unwanted hair on areas like face,arms,armpits,chest,back,bikini,legs...



Handle of EXFU laser hair removal machine

1.12*24mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12*36mm can use at large parts of the body, such as back, arms and legs.....



Authentication

FDA,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

The real experience is visible

Through live test verification ,safe ,long,painless
and effective



Welcome to consult! 7X24 hours online service!