



*D10*

**Portable Hair Removal Machine**

Three bands: 755nm/808nm/1064nm  
Suitable for all skin types



**DIODE LASER** hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm + 808nm + 755nm

**About hair removal machine D10**

- \* USA or Germany imported laser bar 8—12bar.
- \* More than 50 million shots , more than 3 years don't need to change new handle.
- \* 3 waves 1064nm + 808nm + 755nm, 3 in 1 all skin type can be used

# Handle Display

Two colors, two spot sizes are optional



**Triple wavelength included:755nm 808nm 1064nm**

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

# *Working Principle*

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)

# The real experience is visible

Through live test verification ,safe ,long,painless  
and effective



- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option,easy to operate.
- 3) OEM service: your logo can be added on machine screen for free,accept your special language.



# Product details

Ultra-thin large screen, cool light strip



**For more details, please consult us!  
24 hours online!**