

Soprano ICE PLATINUM

Medical beauty machine

Medical diode laser hair removal
For all skin types,
triple wavelength laser work together

Diode laser hair removal machine.

- * No pigmentation. Suitable for any kind of skin;
- * Suitable for any kind of skin ;
- * Safe and Fast.
- * International Hair Removal Golden Standard;
- * The optimal laser wavelength 808nm or 755+808+1064nm;

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

Three Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair) hair removal.
 808nm for yellow (natural) skin hair removal.
 1064nm for black skin (black hair) hair removal.




ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison



Model	Diode Laser platinum
Laser Type	Germany/USA imported 12 bars, 15 bars
Display	14 inch 4K touchable screen
Wavelength	755nm 808nm 1064nm
Shots	40 million shots
Energy	10~150 j/cm ² , adjustable
Frequency	1-10HZ
Cooling	TEC+Air+Water Cooling
Power	3500W
Spot size	12*24mm/12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose



15 Years Laser Beauty Decvice Manuafactor

Make your beauty business easier

For 15 years of integrated production and marketing chemical plant, we have worry-free after-sales service:

Considering the long distance between us and customers, in order to better serve customers,

Our company has established a professional technical after-sales service team.

- 1) Our technicians will solve any machine problems in time and prepare documents for you within 24 hours.
- 2) You can also contact us by telephone, online, etc..
- 3) We provide complete training documents and videos for the machine.

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



Professional OEM ,ODM Services:

- Print any color .
- Add your logo
- Add any language into machine system.
- Design exclusive machine shell for you , form your own brand in market .
- Design new interface and system of machine , make it most convenient to you and your clients.

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

**Welcome to consult and cooperate
24-hour online service!**