



DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

MORE



Diode Laser
Permanent hair removal

Why all the beauty salons & beauticians choice titanium

1. Professional. we have more than 15 years experiences in the High-end beauty machine area.
2. Safety. no side effect on skin and sweat glands, no scar.
3. Fast cooling, which achieve painless hair removal.
4. Popular. Triple wavelength: 755nm+ 808nm+1064nm ,suitable for all the skin types, black skin fine hair all can be easily removed.
5. High energy. Lager spot size, 50 million shots, effectively destroy hair follicles, permanent hair removal.

Handle show

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face,arms,armpits,chest,back,bikini,legs...



- >>> Big spot size 12*20mm, 12*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



12*24mm 1200W handle
Additional therapeutic head



12*36mm 1800W handle
Additional therapeutic head



- >>> New nose hair treatment head, applicable to small part treatment
- >>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Effect

This is the clinical result of hair removal
It takes 3--5 times to realize
permanently hair removal



- * 4K 14 inch Screen, offering super cool touching experience.
- * OEM service is accepted. adjusting parameter is ok.
- * Add your logo and language for free

Specification of Diode Laser Hair Removal Machine

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser medical laser bar :10bars/15bars
Power of each bar	Medical with 120w/Bar
Display system	14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	Medical with 12*24mm ² /12*36mm ²
Laser handle lifespan	At least 40 million shots
Energy	10-150 J / cm ² adjustable (up to 150J/cm ² optional)
Pulse Duration	30~400ms adjustable
Frequency	1.0-10 Hz;
Cooling system	Compressor+air+close water circulation
Handle Power	1000w/1200w/1600w/1800w
Machine Power	4000w
Electrical source	220V/50HZ or 110V/60HZ
Crystal temperature	-20~3°C
Machine temperature	24°C
Power requirement	AC220V/110V 50~60Hz



Professional OEM ,ODM Services:

- Print any color .
- Add your logo
- Add any language into machine system.

- Design exclusive machine shell for you , form your own brand in market .
- Design new interface and system of machine , make it most convenient to you and your clients.

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



aesthetics medical aesthetic machines advanced aesthetics machines diode laser 755 808 1064 diode laser hair removal machine laser hair removal machine

**Please consult us for more details.
24 hours online!**