



1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.
6. Two models can be selected, single handle or double handle



**Most advanced TEC cooling system inside this machine to deliver a super good cooling results. 24 hours working time.Sapphire material.Actual Pain-free experience!**

One minute cooling -21°C

## Best **TEC Cooling** system hair remover laser



- 1) 10 bars/ 12 bars/ 16 bars, 10-40 million shots.
- 2) Big spot 12\*20mm / 12\*35mm for fast hair removal.
- 3) Frozen ice cooling sapphire crystal, for painless hair removal.
- 4) High quality gold laser bar imported from Germany.
- 5) Medical handle as low as 350g easy to treatment.

**1 minute**  
and you're done

35mm {

**FASTER**

Screen system



1. 14 inch big touch screen, humanized designed.
2. Male/female, body parts, 6 skin types for option.
3. 6 language systems, native language + whatever you want.
4. Free OEM program service (logo/system...)

|                         |  |
|-------------------------|--|
| Laser bar               | Germany/USA imported, 8 bar, 10 bar, 12 bars, 16 bars  |
| Wavelength              | 755nm 808nm 1064nm/ or single 808nm  |
| Energy                  | 0-150J/cm <sup>2</sup>   |
| Frequency               | 1-10hz   |
| Pulse width             | 40-800ms   |
| Operative LCD Interface | 14.0 TFT True Color LCD touch screen   |
| Cooling system          | Air and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable |
| Power                   | 4000W  |
| Electrical source       | 220V/50HZ or 110V/60HZ   |
| N.W/ G.W                | 62kg/78kg  |

**Standardized  
production**



**Professional  
Production R & D  
Sales Department**



**Mass production  
of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

## Custom Section


**CASE** design



**LOGO** design



**SYSTEM** design



**Certificate Display**

# CERTIFICATE DISPLAY

