

NEW PRODUCT

D10

Portable Hair Removal Machine

-Convenient and efficient hair removal-



**Permanent laser hair removal diode laser hair removal machine
Germany 755 808 1064 diode laser diode ipl laser hair removal**

Product details

Ultra-thin large screen, cool light strip



Advantages



- * USA or Germany imported laser bar 10bars/15bars
- * More than 50 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used

Working Principle

Suits for all skin and hair types




12*20nm
755nm Laser
808nm Laser
1064nm Laser



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

Products Description

Mini Portable

The net weight of the handle is
about equal to one iphone

285g



Ergonomic handle
It's not tiring to take off

About Handle

1200W/1800W big power for free choice

12*24 or 12*36mm spot size

*285g Medical handle, light weight, free quick slide treatment


* With indicator light, to show working condition(on machine & handle), safely use

1 minute quick frosting, comfortable and painless treatment experience

What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,
the handle can quickly frost.





800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

755+808+1064nm, suitable for permanent hair removal of all skin types



Product parameters



Device Name	Diode Laser Machine
Model Number	Diode Laser D10
Wavelength	755+808+1064nm Technology
Screen size	12inch 4K-HD screen
Lifetime	50 Million shots
Pulse Duration	10-300ms
Laser Bar	100w for each one America Coherent Laser Bar
Frequency	1-10hz
Spot size	12x20mm Spot Size
Energy	1-150J
Cooling System	TEC cooling circulation
Power Of Machine	2500W
Voltage	AC220V 50HZ/60HZ
Demension of machine	380mm*460mm*300mm
Package	Aluminum box
Warranty	2 years for machine 1 year for handle

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

7 * 24 hour online service!
Welcome to consult!