

# DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm +808nm + 755nm



## About hair removal machine D10

- \* USA or Germany imported laser bar 8——12bar.
- \* More than 50 million shots , more than 3 years don't need to change new handle.
- \* 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used

## Handle Display

Two colors, two spot sizes are optional



**Triple wavelength included:755nm 808nm 1064nm**

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

## ***Working Principle***

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)

# The real experience is visible

Through live test verification ,safe ,long,painless  
and effective



- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option,easy to operate.
- 3) OEM service: your logo can be added on machine screen for free,accept your special language.





# Product details

Ultra-thin large screen, cool light strip



**For more details, please consult us!  
24 hours online!**