



40K CAVITATION 5IN1

RF+VACUUM+CAVITATION
+LASER PADS SLIMMING MACHING

START





Advantage



Advantage

- **portable**

5 in 1 salon beauty system

saving shipping cost

5 handles

for slimming, skin tightening, wrinkle removal

- **Advantage**

high power cavitation 300W more effective

vacuum head help a lot for supus fat cell

2 years warranty

multi-color for option





Cavitation

Frequency:4Mhz

Power:150W

Burning explode fat cell



Monopolar RF

Frequency:40khz

Power:300W

Body shape fat reduction



Big tripolar RF

Frequency:4Mhz

Power:150W

Skin tightening lifting wrinkle removal



Small Tripolar RF

Frequency:1Mhz

Power:150W

Skin tightening lifting wrinkle removal



Vacuum

Frequency:1MHz

Pressure:-90kpa

Slimming Remove surplus fat cell

item	Cavitation+Vacuum+RF slimming machine
TFT LCD display	8 inch color touch screen
Technology	Cavitation+Vacuum+RF (monopolar RF+Tripolar RF) Ultrasonic rf cavitation machine head Vacuum liposuction head
Handpieces	Monopolar RF head Tripolar RF head (big) Tripolar RF head (small)
Cavitation frequency	40 khz

Cavitation max power	300w
Tripolar RF	1-10 MHZ (Output frequency) 150 watts (Maximum output power)
Monopolar RF	1-10 MHZ (Output frequency) 150 watts (Maximum output power)
Vacuum pressure	100 KPA
Size	Machine size: 47*31*38 cm Aluminum case packing size: 54*43*46cm
Voltage	220V AC /110V AC
N.W.	15KG
G.W.	25KG

Treatment before & after compare



Application and Treatment Effect:

- >Suitable for 6 different color skin,including the dark skin.
- >The sapphire temperature cools down 0~3°C,clients feel comfortable and painless in whole treatment .
- >Long continuous working time,ensure the works in Clinic/salon use.

AMAZING EFFECT

Before & After



Before


Five weeks later

Eight weeks later



Before

After



Before

After



Before

After



Before

After

Free logo service



[Consult immediately!](#)