

Professional 808nm diode laser hair removal 808 diode laser hair removal machine

- * Suitable to [all types of hair removal](#).
- * [Permanent](#) hair removal.
- * No scar, no any side-effect .
- * TEC Cooling system , 1200W TEC Cooling , can work for [24 hours continuously](#) .

2 YEARS WARRANTY

Smart clinic data center

- Large 12*35 spot size for quick treatment
- TEC continuous cooling system
- Single/Two connectors
- Smart clinic data center
- User friendly large screen
- I-VI skin tones and tanned skin

Most important thing

3 combined wavelengths covering the optimal treatment

Painless Proven safety Permanent hair removal . All skin types, even tanned skin



Advantages of 808nm diode laser hair removal

- 1) Suitable for **any areas hair removal** such as: Face, arms, armpits, chest, back, bikini, legs...
- 2) **Fast treatment**, frequency 1-10hz.
- 3) Suit all skin type and hair type



Hair removal diode laser 808nm handle

- * USA imported bar, energy more stable and strong.
- * Long lifespan, Shots up to 40 million, life maintenance free.
- * Spot size : 10*20mm / 12*35mm * Ice cooling, customers not feel pain at all, comfortable hair removal treatment.
- * Strong power, 12 bar 1200W, fast hair removal. 10 bar 1000W, 16 bar 1600W also available

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

Before



After



Treatment effect



Hair in the treatment area can be easily pulled out



Before




After



Before



After



Before



After

- *12.4 inch intelligent big screen
- * Multi languages available, your own language can be added.
- * Salon, Clinic, your any wanted logo can be added.