



DIODE LASER HAIR REMOVAL MACHINE

*New 3D 755nm 810nm 1064nm technology
Super Ice painless experience
Fast and permanent hair removal*

Vantaggio della macchina per la depilazione laser a diodi 755 808 1064

- 1) Utilizzare il condensatore TEC, ha un migliore effetto di raffreddamento, assicurarsi che la macchina funzioni continuamente per 24 ore, anche in estate.
- 2) Utilizzare la pompa ad alta pressione importata dall'Italia, 40.000.000 di durata della vita più lunga
- 3) 2 filtri, 1 filtro per acqua addolcita, 1 filtro per impurità separato.
- 4) Alta potenza 2000w, forte energia, ottenere un buon effetto di depilazione.

MULTI-ANGLE MACHINE DISPLAY



New upgrade 14-inch HD 4K screen
12*35mm big spot size
Optional parameters for different skin types



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Before and After

Treatment comparison



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



TECHNICAL PARAMETERS

Device Name	Diode laser hair removal machine
Model Number	V30 single handle 4K
Wavelength	755nm 808nm 1064nm
Screen size	14 inch 4K true color touch screen
Pulse Duration	1-300ms
Frequency	1-10hz
Spot size	12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling
Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	45.4cm*52.1cm*101cm
Package	Aluminum box
Warranty	2 years

Per ulteriori informazioni sul prodotto, contattaci online 24 ore su 24!