



Descrizione del prodotto



**Impugnatura per mini laser a diodi**

dimensione spot 14\*14mm, 5 barre 600w

# *Handle Display*

*The handle is small and light, weighing as low as 168.8g.  
Very light to operate*



1) Laser a diodi 755nm 808nm 1064nm □ depilazione per tutti i tipi di pelle 2)  
Raffreddamento ad acqua raffreddamento ad aria raffreddamento a compressore, per una  
depilazione indolore.

# Cooling Effect

*The handle has a cooling effect that improve treatment comfort.*



**Just One minute!**

Quick cooling down to

**-25°C**

## Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)

# 6<sup>+</sup> ADVANTAGE

HANDLE OF 808 DIODE LASER DEVICE



No pain



No side  
effect



Germany  
imported bar



Big spot  
15\*25mm



super cooling  
system



Permanent  
hair removal



# Before and After


Treatment comparison



# Screen Display

*13.3 inch 4K true color touch screen*

*The display screen is clear at a glance and easy to operate*



*6 language for your choice. Super cool touch Experience .*

*Special language can be added according to your actual requirements.*

*Your logo also can be added on diode laser screen.*

1. Touch screen da 13,3 pollici, progettato umanizzato
2. Maschio/femmina, parti del corpo, 6 tipi di pelle per opzione.
3. Inglesela tua lingua madre.
4. Servizio di programma OEM gratuito (logo/sistema...)

# We have OEM Services

Serving your needs

Language  
System  
program



Appearance



Screen/Machine  
LOGO



Colors



Other  
customization





Product Customization Design



Production and Processing



Program Debugging



Machine Debugging



Batch Production



Fine and Safe Packaging

Confezione del prodotto

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service