



Vantaggi della macchina per la depilazione della famiglia portatile

- 1) mostra che il volume generale della macchina è molto piccolo.
- 2) La maniglia del display è piccola, la maniglia da 168 g è molto leggera
- 3) La macchina è un compressore con alta efficienza di refrigerazione e basso rumore
- 4) La macchina è leggera e facile da trasportare

Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

Mini manico laser a diodi, taglia 14 * 14mm, 5 bar 600W

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!
Quick cooling down to

-25°C

- 1) Laser a diodi 755nm 808nm 1064nm, depilazione per tutti i tipi di pelle
- 2) Raffreddamento ad acqua raffreddamento ad aria raffreddamento del compressore, per depilazione indolore.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. Touch screen 13.3 pollici, progettato umanizzato
2. Maschio / femalo, parti del corpo, 6 tipi di pelle per opzione.
3. Italiano la tua lingua madre.
4. Servizio del programma OEM gratuito (logo / sistema...)

We have OEM Services

Serving your needs



La nostra fabbrica

Weifang Sunshinekj Electronics Co., Ltd (Abbreviazione: MLKJ) è un produttore altamente professionale ed experienced di attrezzature di bellezza in Cina, ha 14 anni in industria della bellezza

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- **OEM & ODM**
SERVICE



13 Years Laser Beauty Decvice
Manuafactor

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE



Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. Abbiamo una produzione professionale R & DDEpartment, può fornire supporto tecnico, garanzia di 2 anni



Imballaggio del prodotto

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service