



**2021 WINNER  
EUROPEAN  
PRODUCT  
DESIGN  
AWARD**

[illegible]



808 nm laser treatment for hair removal, the wavelength is 808nm?

The laser is a diode laser, the wavelength is 808nm, the power is 10W.

755 (nm) 808nm 1064nm, the laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser.

The laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser, the wavelength is 808nm.

The laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser, the wavelength is 808nm, the power is 10W.

The laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser, the wavelength is 808nm, the power is 10W.

**weight 450g**


The handle weighs only 450g, making the treatment process easier

12\*20mm      12\*35mm      12\*20mm      12\*35mm

The laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser, the wavelength is 808nm, the power is 10W.

The laser is a diode laser, the wavelength is 808nm, the power is 10W, the laser is a diode laser, the wavelength is 808nm, the power is 10W.

# Laser show Handle laser bar optional



1064nm 808nm 755nm 3 1064nm 808nm 755nm.

1064nm 808nm 755nm 1064nm 808nm 755nm.

1064nm 808nm 755nm ICE PLUS. 1064nm 808nm 755nm.

24 1064nm 808nm 755nm.



**Just One minute!**  
Quick cooling down to **-25°C**



□□□□□□ □□□□

# Treatment Comparison



000 00000 00000 000000  
 0000 000 , '0000 14 00000 0000 000  
 0000 00000 00000 000 0000 6 , 000 0000 6 , 00000 000 2.  
 000 000 000 00 000000 0000 , 000 00000000 6 .3  
 000000 00000 4 OEM 000/00000/00000/000) 00000...

## FREE LOGO SERVICE





# 14 Years Laser Beauty Decvice Manuafactor

- High Feedback Top10 Supplier
- OEM & ODM SERVICE



1. 我们拥有14年的激光美容设备制造经验，产品远销全球102个国家。  
 2. 我们拥有完善的质量管理体系，产品出厂前经过严格检测，确保质量。  
 3. 我们拥有专业的研发团队，可根据客户需求定制各种规格的产品。

## Certificate display

Certificate is the best guarantee for you



我们拥有14年的激光美容设备制造经验，产品远销全球102个国家。



|             |                                               |
|-------------|-----------------------------------------------|
| □□□□□       | □□□□□ □□□□□ V28                               |
| □□□□□ □□□   | □□□□ 16 ,□□□□ 12 ,□□□□ 10 ,□□□□ □"□□□□/□□□□□□ |
| □□□□□□□□    | 4 '□□□□ 15.6----14 □□□□K □□□□ □□□□□           |
| □□□ □□□□□   | 755 □□□□□□ 1064 □□□□□□ 808 □□□□□□             |
| □□□□□□      | 40 □□□□□ □□□□□□                               |
| □□□□□□□□□□  | 10~150 j/cm2, □□□□□□□□                        |
| □□□□□□□     | 1-10HZ                                        |
| □□□□□□□□□□  | TEC□□□□□□□□□ □□□□□□                           |
| □□□□□□□     | 3500W                                         |
| □□□□□□ □□□□ | 12*20 □□□□□□ □"□ 35*12/□"□                    |
| □□□□        | 110V/60HZ 220 □□V/50HZ □□□□□□□                |
| □□□□ □□□□   | 95 □"□                                        |
| □□□□□□ □□□□ | 105 □"□                                       |
| □□□□□□ □□□□ | 45*52*110 □"□                                 |
| □□□□□□ □□□□ | 56*70.4*125 □"□                               |

□□□□□□ □□□□ □□□□□ □□□ 3-7 :□□□□□□ □□□□

□□□□□□□ :□□□□□□ □□□, **DHL, TNT, Fedex** □□□□□□ □□□□ □□  
 □□□□□□□□ □□□□□ □□□□□□ :□□□□□□ □□□□□  
 □□□□□ □□□ □□□□□□ □□□□ □□□□□ □□□□□ ,□□□□□□□□ :□□□□□□ □□□□□

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,



# CONTACT US



## In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month