




1.3 1064 nm 808 nm 755nm, 1-3 1000 :1200W/1600W ! 35*12 , 20*12 . 3 Dual-TEC , 24 . 4

Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)







Different spot size Handle color optional



□□□□ □□□□ □□□ □□□□ □□□□□

Alex 755nm □□□□ □□□□

808 □□□□□□ □□□□□nm □□□□ □□□□

Long Pulse 1064nm □□□□ □□□ □□□□

Treatment effect



□□□□

1. □□□ □□□□ 6 □□□□□□ □□□□ □□□□□□ ,□□□□ □□□□ 6 ,□□□□□□ □□□□ □□□ □□□ □□ □□ □□ □□ □□□□□□ □□□□□□ ,□□□□ □□□□□□□□□□ 6 .2
- □□□□□□ .3 OEM □□□□□□/□□□□□□) □□□□□□...

