

Stronger, Faster

×

14-inch HD 4K Screen



□□□□ □□□□

----- □□□□□□ □□□□□□ □□□□ □□□□ ,□□□□ □□□□ ;□□□□□ □□□□ □□□□ □□□□□□□□ □□□□;

----- □□□□□□□□ ,□□□□□□□□ ,□□□□ ,□□□□ ,□□□□ □□□□ ,□□□□□□□□ □□□□□□ □□□□□□ □□□□□□□□□□...

----- 808 □□□□□ □□□□□□ □□□□□□nm 1064 808 755 □□□□nm, □□□□□□□□□ □□□□□□ □□□□ □□□□□□.

----- 1 1-10 □□□□□□□□□□□□□□□□□□□□□□□□Hz. □□□□ □□□□□□!!! -

NEW



NEW



NEW



.ﺩﺭﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍ ﺩﺍﺩﺍ ﺩﺍﺩﺍ ,ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍ ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍﺭﺍﻥ
ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍ 24 ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍﺭﺍﻥ ﺩﺍﺩﺍ ﺩﺍ!

Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



□□□□ □□

350g lightweight **handle**, more ergonomic

Available in **black or white**





} 35mm



before after

Large 3.5cm spot size, and integration of three wavelengths
Hair removal is quick, efficient and convenient




One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser




laser rod imported from America.10million—40million shots.Permanent hair removal



755 808 1064nm □□□□ □□□ □ □□ □□□□ □□□ □□□□□□ □□□□□□□□ □□ □□□□□□□□□□..

*. " " " " " " " " " " " " " " " "
 (" " " " " " " " " " " ") " " " " " " 10-40 *
 12 " "10 *bar 16bar, " " " " " " .

* 1000 ㎓ ㎓㎓㎓ ㎓㎓㎓W / 1200W / 1600W,



□□□□ □□□□

Before and After

Traetment comparison





Customer feedback

Ratings&Reviews



m*****a
Georgia

Supplier Service: **Very satisfied** (5 stars)

06 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



Big hug with Maggie, she is very kindness and professional. Weifang Mingliang Electronics Co., Ltd is the best supplier , with high quality and professional package.

If you also need laser machine, strongly recommend them.

0



A*****
Mexico

Supplier Service: **Very satisfied** (5 stars)

01 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



estoy muy feliz con mi compra, me llevo mi pedido a tiempo con buen empaque, espero que todo marche bien.. Maggy una excelente persona y vendedora espero tener más compras a futuro gracias

0



M*****a

Supplier Service: **Very satisfied** (5 stars)

20 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



Professional high Power 1600W diode laser hair remo...



super

0



0000 000 00000 0000 , '0000 **14** 00000 00000 0000 000 000 * 000000 **808** 00000 00000
 .000000
 00000 * **OEM** .0000 000000 000000 .00000
 00000 000 00000 00000 00 0000 *