



From Israel Technology

FOR ALL SKIN TYPE HAIR REMOVAL

- 100% Ice Cooling
- 100% Permanent
- 100% Painless

.00000 000000 0000 000000 000000
 ;000 00 000 000 000000 .0000000000 0000*
 ;000 00 000 000 000000 *
 .000000 00000 *
 ;00000 00000000 00000000000 00000 00000 *
 808 0000000000 00000000 00 00000 *nm 7558081064 00nm;

350g
 Ultra light handle



12×24 mm
Handle
 1200W diode laser hair removal




12×36mm
Handle
 1800W diode laser hair removal

00000 **Three Waves 755 nm 808nm 1064nm**, 0000000 0000 00000 000 00000000 000000.

755nm .(00000/00 00000) 0000 00000 00000 0000000

808nm .() () () () ()
1064nm () () () () () () () ().




ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison

