

Trending Model 1600W Laser 4K Smart Screen

☐	☐	☐	☐	☐	☐	☐	☐
--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------




□□□□□□

1.3 1064 nm □□□□nm 808 nm Alex 755nm, 3 □□□□ □□□□ □□□□□□ □□□□ 1-□
1000 □□ □□□□ □□□□ :□□□□ □□□□W/1200W/1600W □□□□□□□□□□


!□□□□ □□□□ □□□□ □□□□□□ □□□□, □"□ 35*12, □"□ 20*12 □□□□□□ □□□□ □□□□ .2

□□□□□□ □□□□□□ :□□□□□□ □□□□□□ .3 Dual-TEC □□ □□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□□□□□, □□□□□□□□□□
.□□□□□□ □□□□ □□□□ □□□□ 24, □□□□□□


□□□□□□ □□□□□□ □□□□□□ :□□□□□□□□ □□□□ .4



A natural



B energy absorbed by hair



C hair follicle died

□□□□ □□□□ □□□ □□□□ □□□□□

Alex 755nm □□□□ □□□□

808 □□□□□□ □□□□□nm □□□□ □□□□

Long Pulse 1064nm □□□□ □□□ □□□□


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



□□□□ □□□□ & □□□□□□

1. □"□□□□ □□□□ □□□□ □□ :□□□□ □□ Coherent/□□□□ Dilas2. 3 755 :□□□□nm 808nm 1064nm 3 1-□
- "□ 35*12 ,□"□ 20*12 :□□□□□ □□□□ .3
4. 1000 □□□□ □□□□ :□□□□W 1200W 1600W & OEM
3. □□□□□□ □□□□□□ □□□□ 24 ,□□□□ 1 □□□ □□□□□□ □□□□□□ □□□□□ □□□□ :□□□□□□



35mm

before after

Large 3.5cm spot size, and integration of three wavelengths
Hair removal is quick, efficient and convenient

□□□□□ □□□ □□□□□□□

□□□□□ □□□□□ Super TEC □□□□□ □□□ □□□□□ □□□□□

22- □□□□□ □□□□□□ □□□□□□□□□□°C

Before and After

Treatment comparison



□□□□□

1. □□□ □□□□ 6 □□□□□□ □□□□ □□□□□ □□□□ ,□□□□ □□□□ 6/□□□□□□ □□□ □□ □□□□□□ :□□□□ □□□□□□□□ □□□ □□□ □□□ □□ □□□□□□□□ □□□□□ ,□□□□ □□□□□□□□□□ 6 .2 □□□□□□□□ □□□□□□ .3 OEM □□□□□□/□□□□□□) □□□□□□...)

