



1. 532nm 755nm 1320nm 1064nm
 q switch nd yag 532nm 755nm 1320nm 1064nm
 532nm 755nm 1320nm 1064nm




1. 532nm 755nm 1320nm 1064nm 532nm 755nm 1320nm 1064nm

2. 532nm 755nm 1320nm 1064nm 532nm 755nm 1320nm 1064nm

3. 532nm 755nm 1320nm 1064nm 532nm 755nm 1320nm 1064nm

532nm 755nm 1320nm 1064nm 532nm 755nm 1320nm 1064nm

4. 1064nm 532nm 1320nm 755nm



1064nm 532nm 1320nm 755nm

1. 1064nm 532nm 1320nm 755nm .1064nm 532nm 1320nm 755nm .
 2. 1064nm 532nm 1320nm 755nm 1064nm 532nm 1320nm 755nm .
 3. 1064nm 532nm 1320nm 755nm 1064nm 532nm 1320nm 755nm .
- 1064nm 532nm 1320nm 755nm

How is it different?



5. EXFU is a medical laser device that is used for various skin treatments.

1. 532: This is a short-pulse laser that is used for treating pigmentation and vascular lesions.

2. 755: This is a long-pulse laser that is used for treating hair removal and skin rejuvenation.

3. 1064: This is a long-pulse laser that is used for treating skin rejuvenation and vascular lesions.

4. 1064: This is a long-pulse laser that is used for treating skin rejuvenation and vascular lesions.

5. 1320: This is a long-pulse laser that is used for treating skin rejuvenation and vascular lesions.

Advantage

The maximum energy, the best effect

Laboratory data shows that the laser rod reaches 2000mj.
Precise calculation of laser value
The aiming distance of the indicator light is 6-10cm

5 treatment heads

Detachable and rotatable outer wire design

532: Remove colored tattoos.

755:honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin


Adjustable parameter 1064: for tattoo removal, eyebrow clearing

1064: used for removing tattoos and clearing eyebrows

1320: large area treatment, large spot, fast treatment speed and good effect

□□□□□□ □□□□□□

Working Principle



TREATMENT HEADS



532: Remove colored tattoos.



755 honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin



Adjustable parameter 1064: for tattoo removal, eyebrow clearing



1064: used for removing tattoos and clearing eyebrows



1320: large area treatment, large spot, fast treatment speed and good effect

Product Features



Tattoo removal

Eyebrow embroidery removal

Freeline removal

Eyeline removal

Whitening

Skin rejuvenation

Lipline removal

Pigment treatment

1. 2000-20000mj, 2000-20000mj, 2000-20000mj

1. 2000-20000mj, 2000-20000mj, 2000-20000mj

2. 2000-20000mj, 2000-20000mj, 2000-20000mj

3. 6-10mm, 6-10mm, 6-10mm


2000-20000mj

1064nm

Precise Calculation Laser Value

The aiming distance of the indicator light is 6-10cm

6-10cm



You think you can. you can
No one can stop me




□□□□ □□□□□□ Q-switch □□□□□ □□□ ,□□□□□ □□□□□□ □□ ,□□□□□ □□□□□ Q-switch.


[illegible]

Treatment **Effect**


Tattoo removal





Nevus Ota removal




Eyebrow and eyeliner removal



Lipline removal






BEFORE

AFTER




BEFORE




AFTER



Original pigment



Traditional laser



Picosecond Laser



BEFORE



AFTER

100% 100% 100%

100% 100% '100% 100% 100% 100% 100%


100% 100% 100% 100%

6 100% 100% 100% 100% ,100% 100%

100% OEM 100%/100%/100% 100% 100% ,100% 100% 100% ,100%

Screen Image

The display screen is clear at a glance and easy to operate



10 inch true color big touch screen. Super cool touch Experience.
Special language can be added according to your actual requirements.
Your logo also can be added on diode laser screen.

Picosecond new upgrade

The maximum energy, the best effect


Smallest size

Rational design

5 treatment heads, detachable and rotatable outer wire design
a solution to a variety of skin problems



Picosecond
treatment head
Picoscoud



100% 100% 100%

100% 100%

100%

100% 100%

100% 100%

100%

100%

100% / 100% 100% Nd yag

100% 100% / 100% 100% 100% Blackface

5 100%

1064 100% 755 100% 1320 100% 532 100%

100% 100% 100% 100% 100%....

1-10HZ

110V/220V 50-60Hz

100% 100% 100%

100% 100% 100% 100% 100% 100% 15 100%!

15 100% 100% 100% 100%

100% CE 100% 100% TUV 100% 100% 100% & OEM

Our Showroom



Our products are certified by CE, FDA, TUV, ISO 13485... etc.

We provide OEM/ODM services for our customers.

We are a professional manufacturer of medical devices. We have a complete production line and a professional R&D team. We can provide you with the best quality products and the most competitive prices.

CERTIFICATES



BV-France's most authoritative
certification body BV Group certification



TUV-Germany's most authoritative
certification body Rheinland certification



SGS-Switzerland's most authoritative
certification body SGS certification



Italy ECM Certification



ISO 13485

NQA medical system
certification



Production Process



Warehouse spare parts



Parts assembly



Precision machining



Handle fabrication



Product assembly process



Quality inspection
of finished products



Product packaging

, 明光电子 拥有 完整 的 生产 流程 , 从 原材料 的 采购 到 成品 的 交付 , 每一个 环节 都 严格 按照 标准 执行 。 明光电子 拥有 24 小时 生产 能力 , 能够 快速 响应 客户 需求 。 明光电子 拥有 先进 的 生产设备 和 技术 人员 , 能够 生产 出 高质量 的 产品 。 明光电子 拥有 完善 的 质量管理体系 , 能够 确保 产品 的 质量 和 稳定性 。 明光电子 拥有 完善 的 售后服务 体系 , 能够 为客户提供 及时 的 技术支持 和 售后服务 。 明光电子 拥有 完善 的 物流 体系 , 能够 确保 产品 的 及时 交付 。 明光电子 拥有 完善 的 财务 体系 , 能够 确保 公司 的 财务 健康 和 稳定 发展 。 明光电子 拥有 完善 的 人力资源 体系 , 能够 吸引 和 留住 优秀 的 人才 。 明光电子 拥有 完善 的 企业文化 体系 , 能够 增强 员工 的 凝聚力和 归属感 。 明光电子 拥有 完善 的 社会责任 体系 , 能够 为社会 做出 贡献 。 明光电子 拥有 完善 的 环保 体系 , 能够 保护 环境 和 节约 资源 。 明光电子 拥有 完善 的 安全 体系 , 能够 确保 员工 的 安全 和 健康 。 明光电子 拥有 完善 的 保密 体系 , 能够 保护 公司 的 商业秘密 和 知识产权 。 明光电子 拥有 完善 的 法律 体系 , 能够 确保 公司 的 合法 经营 和 合规 发展 。 明光电子 拥有 完善 的 税务 体系 , 能够 降低 公司 的 税务 负担 和 提高 经济效益 。 明光电子 拥有 完善 的 融资 体系 , 能够 确保 公司 的 资金 链 安全 和 稳定 发展 。 明光电子 拥有 完善 的 风险管理 体系 , 能够 识别 和 防范 各种 风险 和 挑战 。 明光电子 拥有 完善 的 战略规划 体系 , 能够 明确 公司 的 发展方向 和 目标 。 明光电子 拥有 完善 的 绩效考核 体系 , 能够 激励 员工 的 积极性和 创造性 。 明光电子 拥有 完善 的 培训 体系 , 能够 提高 员工 的 专业 技能 和 综合素质 。 明光电子 拥有 完善 的 招聘 体系 , 能够 吸引 和 招聘 优秀 的 人才 。 明光电子 拥有 完善 的 薪酬 体系 , 能够 提高 员工 的 薪酬 水平 和 福利待遇 。 明光电子 拥有 完善 的 福利 体系 , 能够 提高 员工 的 生活 质量和 幸福感 。 明光电子 拥有 完善 的 企业文化 体系 , 能够 增强 员工 的 凝聚力和 归属感 。 明光电子 拥有 完善 的 社会责任 体系 , 能够 为社会 做出 贡献 。 明光电子 拥有 完善 的 环保 体系 , 能够 保护 环境 和 节约 资源 。 明光电子 拥有 完善 的 安全 体系 , 能够 确保 员工 的 安全 和 健康 。 明光电子 拥有 完善 的 保密 体系 , 能够 保护 公司 的 商业秘密 和 知识产权 。 明光电子 拥有 完善 的 法律 体系 , 能够 确保 公司 的 合法 经营 和 合规 发展 。 明光电子 拥有 完善 的 税务 体系 , 能够 降低 公司 的 税务 负担 和 提高 经济效益 。 明光电子 拥有 完善 的 融资 体系 , 能够 确保 公司 的 资金 链 安全 和 稳定 发展 。 明光电子 拥有 完善 的 风险管理 体系 , 能够 识别 和 防范 各种 风险 和 挑战 。 明光电子 拥有 完善 的 战略规划 体系 , 能够 明确 公司 的 发展方向 和 目标 。 明光电子 拥有 完善 的 绩效考核 体系 , 能够 激励 员工 的 积极性和 创造性 。 明光电子 拥有 完善 的 培训 体系 , 能够 提高 员工 的 专业 技能 和 综合素质 。 明光电子 拥有 完善 的 招聘 体系 , 能够 吸引 和 招聘 优秀 的 人才 。 明光电子 拥有 完善 的 薪酬 体系 , 能够 提高 员工 的 薪酬 水平 和 福利待遇 。 明光电子 拥有 完善 的 福利 体系 , 能够 提高 员工 的 生活 质量和 幸福感 。

明光电子

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month