

NEW ! Technology



1064 808 755 [www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#)

1. 755 808 1064 [www.meritmedical.com](#)

.[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) .2

.[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) ,[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) .3

[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) ,[www.meritmedical.com](#) [www.meritmedical.com](#) ,[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) ,[www.meritmedical.com](#) [www.meritmedical.com](#) [www.meritmedical.com](#) .4



5. በሙሉ ስራ ላይ የሚገኝ የሙሉ ስራ ላይ TEC 3 ,የሙሉ ስራ ላይ 24.ሰዓት 1-ሰዓት
በሙሉ ስራ ላይ 1/5 ሰዓት በሙሉ ስራ ላይ ሰዓት ሰዓት ,ሰዓት 35*12 በሙሉ ስራ ላይ ሰዓት ሰዓት .6
በሙሉ ስራ ላይ ሰዓት ሰዓት .7.






* 4 0000 00000 000K .000000 0000 000 000000 00000 ,0000 14 00000
 00000* OEM .0000 000000 000000 .00000
 00000 000 00000 00000 00 0000 *
 0000 0000

12*20mm or 12*35mm handle



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...





High-quality **laser bars** imported from **USA**



➤ 10bar
1000W



➤ 12bar
1200W



 16bar
1600W

1000/1200/1600_W high power

Fast hair removal

- * 10-40 (1000w 1200w 1600w) 1000w 1200w 1600w
* 1000w/1200w/1600w 1000w 1200w 1600w



755 808 1064nm 光線の透過率を測定した。透過率は波長によって異なる。透過率は波長によって異なる。