



24 ชั่วโมง !!

350g lightweight **handle**, more ergonomic

Available in **black or white**



755 808 1064 1000 1200 1600 35mm 1D 1D 1D

1000 10,1" 20*12 1000 1000w.

1200 12,1" 35*12 1200 1200w.

1600 16,1" 35*12 1600 1600w.

1000 1000 1000 1000,100000 1000

1000 1000 1000 100000 100000 10 10000 100 100 10000 100 10000



755 808 1064 000000 000000 0000 000000 0000 0000

- 1) 000000 0000 000000 00000000 0000 0000
- 2) 0000 0000 000 000000 0000000000 0000 0000
000000 000 00000 000000 ,0000 00000000 0000 00000000 (3.



00000 0000 000 000 ,0000000 000000 00000




00000 000000
 000000 00000 00000 ,0000 14 .1 0000 000 000
 .0000000 000 0000 6 ,000 0000 ,0000/000 .2

.3
 OEM () ...)

The new 14-inch 4K screen

Support system customization



参数 表

波长	755 nm808nm1064nm
脉冲宽度	16 --- 8 ,ms
光斑大小	100 mm
治疗头大小	14 mm
治疗深度	808nm 808 nm755nm1064nm
治疗面积	12*35 20*12/cm²
治疗头大小	808 10,000,000-40,000,000 J/cm² :J/cm²
治疗头大小	10-150 J/cm² 150 J/cm²
治疗头大小	40 ~ 800ms
治疗头大小	1.0-10 mm;
治疗头大小	TEC 1000W/1200W/1600W
治疗头大小	800W/1000W/1200W/1600W
治疗头大小	2000W
治疗头大小	220V/50HZ 110 V/60HZ
治疗头大小	-10~3 mm
治疗头大小	27~31 mm
治疗头大小	AC220V/110V 50~60Hz

□□□□□□ □□□□□□ ,□□□□□□ □□□□ □□□□□!