



24 小時服務熱線：400-888-8888。歡迎預約諮詢，地址：廣東省深圳市福田區。

Diode Laser

For You. For Life.



00000 000000 0000 000000 00000 1064 808 755 00 000000

- 1) 0000 00000 TEC, 00000 ,0000 24 0000 0000 00000 000000 0000 ,0000 000 00000 0000 00 00 .0000
- 40,000,000-0 0000 0000 0000 0000 ,0000000 0000000 0000 000 0000000 000000 (2
- .00000 0000000 0000 1 ,000 0000000 0000 1 ,0000000 2 (3
- 1600 0000 0000 000 (4w, 000 00000 00000 0000 000 ,00000 0000000.

350g lightweight **handle**, more ergonomic

Available in **black or white**



755 808 1064 1000 1200 1600 350g 350g 350g

1000 10,1" 20*12 350g 350g w.

1200 12,1" 35*12 350g 350g w.

1600 16,1" 35*12 350g 350g w.

350g 350g 350g 350g ,350g 350g

350g 350g 350g 350g 350g 350g 350g 350g 350g 350g



755 808 1064 000000 000000 0000 000000 0000

- 1) 000000 0000 000000 00000000 0000 0000
- 2) 0000 0000 000 000000 0000000000 0000 0000
- 000000 000 00000 000000 ,0000 00000000 0000 00000000 (3.



00000 0000 000 000 ,0000000 000000 00000



00000 000000
 000000 00000 00000 ,0000 14 .1 0000 000 000
 .0000000 000 0000 6 ,000 0000 ,0000/000 .2

波長	755nm808nm1064nm
照射時間	0~16秒 8段階調節可能
照射面積	100mm ²
照射深さ	最大14mm 照射深さ調節可能
照射モード	808nm 808nm755nm1064nm
照射時間	12*35mm 20*12mm
照射強度	808nm 10,000,000~40,000,000 J/cm ² :照射時間
照射速度	10~150 J/cm ² 150 J/cm ² 照射時間
照射温度	40 ~ 800ms 照射時間
照射温度	1.0~10℃;
照射温度	照射温度調節可能 TEC制御 照射温度調節可能
照射温度	800w/1000w/1200w/1600w
照射温度	2000W
照射温度	220V/50HZ 110V/60HZ
照射温度	-10~3℃ 照射温度調節可能
照射温度	27~31℃ 照射温度調節可能
照射温度	AC220V/110V 50~60Hz

□□□□□□ □□□□□□ ,□□□□□□ □□□□ □□□□□!