




1.3 1064nm 808nm Alex 755nm, 3

1000W/1200W/1600W


38*12, 20*12

Dual-TEC


24



A natural



B energy absorbed by hair



C hair follicle died

□□□□ □□□□ □□□ □□□□ □□□□□

Alex 755nm □□□□ □□□□

808 □□□□□□ □□□□□nm □□□□ □□□□

Long Pulse 1064nm □□□□ □□□ □□□□


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



□□□□ □□□□ & □□□□□□

1. □"□□□□ □□□□ □□□□ □□ :□□□□ □□ Coherent/□□□□ Dilas2. 3 755 :□□□□nm 808nm 1064nm 3 1-□
- "□ 35*12 ,□"□ 20*12 :□□□□□ □□□□ .3
4. 1000 □□□□ □□□□ :□□□□W 1200W 1600W & OEM
3. □□□□□□ □□□□□□ □□□□ 24 ,□□□□ 1 □□□ □□□□□□ □□□□□□ □□□□□ □□□□ :□□□□□□



Custom Section

CASE design



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

