



.00000 000000 0000 00000 000000  
;000 00 000 000 000000 .00000000000 0000\*  
;000 00 000 000 000000 \*  
.000000 00000 \*  
;00000 000000000 00000000000 00000 00000 \*  
808 00000000000 000000000 000 00000 \*nm 7558081064 00nm;

**350g**  
Ultra light handle



12×36mm

**Handle**

1800W diode laser hair removal



12×24 mm

**Handle**


1200W diode laser hair removal

Three Waves 755 nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm.

755nm (Alexandrite) 755nm 808nm 1064nm

808nm (Diode) 755nm 808nm 1064nm

1064nm (YAG) 755nm 808nm 1064nm.






**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )




**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)



# Treatment Comparison





Emergency stop button

12 inch big screen quick touch easy operate

Diode laser handle

Vents

Plug

1. 15.6 inch big screen

1. 15.6 inch big screen
2. 12 inch big screen quick touch easy operate
3. Diode laser handle
4. Plug
5. Vents
6. Emergency stop button

12 inch big screen quick touch easy operate!