

Diode Laser

ice Hair removal



1200 0000 00000W 1800W Sopran Titanium

1. 000000 0000 0000 000 00000 ,0000 00000 00000
2. 0000 36*12 0000 ,0000 24*12 0000 0000 :000000
- 1-10 0000 :0000 000000 .3Hz, 00000000 000000 0000.
- 000000 000000





0000 000 000000 000000
000000 00000 000 ,0000 00000000 000000



〇〇〇〇 〇〇〇〇 〇〇〇〇〇 〇〇〇〇〇 〇〇〇〇 **Sopran Titanium**

.〇〇〇〇〇 〇〇〇〇〇〇〇 〇〇〇〇〇 〇〇〇〇 〇〇〇〇 〇〇〇〇 ,〇〇〇〇 〇〇 〇〇〇〇〇 〇〇〇〇〇〇 〇〇〇〇〇〇 〇〇〇〇〇 〇"〇 24*1.12 〇〇〇〇〇 〇〇〇〇〇〇〇 〇〇〇〇〇 ,〇〇 〇〇〇〇 ,〇〇〇〇 〇〇 〇〇〇〇〇〇 〇〇〇〇〇〇 〇〇〇〇〇〇 〇〇〇〇 〇"〇 36*2.12.....

Arm hair removal



Face hair removal



Lip hair removal



Leg hair removal



Back hair removal




Underarm hair removal



Bikini hair removal





755 : 755nm 808nm 1064nm

755nm . 755nm 755nm 755nm 755nm

808nm . 808nm 808nm 808nm 808nm

1064nm 1064nm 1064nm 1064nm 1064nm.

Medical 1200W/1800W

50 Million Shots

USA / Germany Imported Laser Bar



755nm+808nm+1064nm



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)

10 1200 W15bar 1800W

* () .

20-50

1064 808 755 *nm



000 00000

1). 0000 14 00000 00000 000 000 00000 :0000 0000

.000000 00 ,000 0000 00 00000 000000 :000 000000 (2

000000 (3 OEM: 000 00000000 0000 00 000 ,000000 000000 000 00 000 000000 00 0000000 00000.

4K 14 inch HD screen system

