



00 000 CE Medical, ISO13485, 00000000
 0000 000000 ,0000000 000000.
 000000 00 0000 0000 0000 000000 00000 0000 0000 00000000 0000.
 00000 00000000 0000 000000 000000.
 000000 000 0000 000000 000000.
 0000000 00000 0000.
 0 00000 ,000000 00000000 0000000 000000-YouTube 00000000.



0000 0000
 000000 0000 0000 0000000 000000 Ice Platinum
 1. .0000000 0000 0000 000 000000 ,0000 000000
 1000 :000000 .2W 1200 00W, 0"0 35*12 0000 ,0"0 20*12 000 0000 0000
 1-10 000 :0000 000000 .3Hz, .0"00000 00000000 000000 000
 1200 000000 00000000000000 :0000 12 000000 000000 .4W TEC ,°C24 000000 000 00000000000 000000 ,00000000

000000 0000 0000 000000 0000 000 0000 00 ,0000 00 00000000

One minute cooling -27°C

Best **TEC Cooling** system hair remover laser



□□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ □□□□

. 0.000000 0.000000 0.000000 0.000000 0.000000 0.000000 , 0.000000 0.000000 0.000000 0.000000 0.000000 0.000000 " 20*1.12 0.000000

□□□□ □□□□ ,□□ □□□□ ,□□□□ □□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□ 35*2.12

[illegible]

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong

1200<<W power of hair removal on the whole body;

>>1-10Hz fast □□□□□□

>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for **fast treatment**. moderate melanin absorption level making it **safe for darker skin types**. ideal for treating the arms, legs, cheeks and beard.

1064nm

low melanin absorption, focused solution for darker skin types. Offers the **deepest penetration** of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area





Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser energy is absorbed by the melanin in the hair follicle, which destroys the hair-growing area.
2. The hair follicle is damaged and the hair shaft falls out.
3. The hair follicle is regressed and the hair shaft does not grow back.



1

2

3

--	--	--	--	--	--

□□□□ □□□□□□

□□□□□□□□ □□□□□□ □□□□□ □□□□□□ □□□□□□ □□ □□□□

.0000000 00 '00000 12.4 :000 000 (1

6 (2)

000000 0000 0000 000 0000 00 000 000000 00 0000 0000 ,000000 000 (3

55

□□□□□□ □□□□□□ □□□□ □□□□ □□□□□□

12000W 12000W
12000W 12000W
12000W 12000W
12000W 12000W

Energy

Frequency

Frequency

12000W 12000W

12000W 12000W

12000W 12000W

12000W 12000W

12000W 12000W 12000W 12000W
12000W 12000W 12000W 12000W
12000W 12000W 12000W 12000W

40 12000W 12000W

10~150 j/cm2, 12000W

40 ~ 800ms 12000W

1~10Hz

12000W TEC 1200W

12000W 12000W 12000W

12000W 12000W 12000W 12000W

12000W 12000W 12000W

12*20 12000W 35*12 12000W

-10~3 12000W 12000W

AC220/110V, 50/60HZ

Custom Section


CASE dedign



LOGO design



SYSTEM design



12000W 12000W



公司 mingliangkj:

Weifang Mingliang Electronics Co., Ltd (公司简称:MLKJ) 公司主要从事 电子产品 的研发 生产 销售 服务 等业务 , 公司 拥有 先进 的生产 设备 , 完善 的质量 管理体系 , 产品 远销 欧美 日韩 等 地区 , 深受 客户 的 好评 . 公司 秉承 “ 以人为本 , 诚信经营 ” 的宗旨 , 为客户提供 优质 的产品 和 服务 . 公司 地址 : 山东省 潍坊市 潍城区 东风 街 100 号 . 公司 电话 : 0536-2631111 . 公司 网站 : www.mingliangkj.com

□ □□□□ ,□□□□□□

□□□□□□□ □□ □□□□□□ □□□□□□ □□ □□□□□□□ ,□□□□□ □□□□□□□ □□□□ 13 □□ □□□□ □□□□□□ .□□□□□ □□. □□□□ □□□□□

1-□.Weifang Mingliangkj electronics Co., Ltd (□□□□□□ □□□□:MLKJ) □□□□□□ □□□□□□□ □□□□ 15 □□ □□□□□□ □□□□□ □□□□□□ □□□□ □□□□□ □□□ □□ .2
□□□□□□ □□□□□ □□□□□□ □□□□□ □□□□□□ ,□□□□□ □□□□ □□□□□□ .3.

PACKING

safe and thoughtful packaging seivice



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service