







.....

1.
 2.
 3. TEC,
 4. 755 :, nm 808nm1064nm,
 5. 20-40,
-






Laser show Handle laser bar optional



⊙ 10bar


⊙ 12bar

⊙ 16bar



Working Principle

Suits for all skin and hair types




- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)



□□□□□□ □□□□

Treatment Comparison



.000000 000000 00000 0000000 00
00000000 0000 24!