



2021 Salon Queen

FASTER: 60% FASTER
 STRONGER: STRONGER POWER 40%
 BETTER RESULT
 SMARTER: 4K ANDROID SCREEN

FASTER, STRONGER, SMARTER

1. 40,000,000 shots per session.
2. .40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session.
3. .40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session.
4. .40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session.
5. .40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session.
6. .40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session, 40,000,000 shots per session.



V26

Super comfortable experience
 Painless and permanent treatment result
 Suitable for all skin types and body areas

TEC 24 10 16 12 35*12 / 20*12 2 3 4 5

24 10 16 12 35*12 / 20*12 2 3 4 5



1) 10 16 12 35*12 / 20*12 2 3 4 5

. 35*12 / 20*12 2 3 4 5

2) 3 4 5

4) 5

5) 350

1 minute
and you're done



35mm

FASTER

14 1

6 2

6 3

4 OEM

16 12 10 8	755nm 808nm 1064nm/ 808 nm
0-150J/cm2	
1-10	
40-800ms	
LCD 14.0 TFT True Color	

□□□□□□
□□□□ □□□□
N.W/ G.W

4000W
220V/50HZ 110 □□V/60HZ
62 □"□ 78/□"□

Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design




□□□□ □□□□



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

