

Why

choose us?

14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier


60000+ customers in 102 countries

The products are sold to 102 countries, serving more than 60,000+ customers

2 years warranty

2 years warranty for each machine All question will be response within 24 hours solved within 72 hours

Make Your Beauty Business More Easier !



1. 14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier A.ODM / OEM B. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier C. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier D. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

2. 60000+ customers in 102 countries

DIODE LASER

*3 waves 1064nm + 808nm + 755nm,
*Safe, Fast, Painless, permanent
*For all skin and hair style hair removal

>>>

1. 14 years factory

2. 60000+ customers in 102 countries

3. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

4. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

000 0000 6 00 '0000 5.14.0 00000 00000 000000 000 000.

Machine display

Show the machine from three angles, looking at the machine comprehensively.




MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY



00000 0000



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)


□□□□ □□□□□□



□□□□□ □□□ 10-300ms □□□□□□□□
 □□□□□□ □□□□□□□□ -27°C~5°C
 □□□□□ □□ 10bar/12bar/16bar, □"□□□□/□□□□□□□□ □□□□□
 □□□□□□□□□□□□□□ 7558081064 □□□□ □□□nm □□□□□□□□□□
 □□□□ □□□ 1000w/1200w/1600w
 □□□□□ □□□ 808 □□□□□ □□□□□nm 755/808/1064 □□nm 3 □□□□□□□ □□□□
 □□□□□ □□□□□ □□□□□ 12 □□□□'
 □□□□ □□□□□ 755/808/1064

操作时间	20-40 分钟 可调
能量密度	10~150 j/cm2, 可调
频率	1-10HZ
输出功率	3500W
屏幕尺寸	12*20 英寸 35*12 厘米
电压	110V/60HZ 220 V/50HZ 可调
重量	95 公斤
尺寸	53*40*105 厘米

其他参数



其他参数

1. 6.3 英寸触摸屏 分辨率 640*480 , 功率 60W , 重量 14 公斤 , 尺寸 140*40*105 厘米 , 电压 110V/60HZ 220 V/50HZ 可调 , 频率 1-10HZ , 能量密度 10~150 j/cm2, 可调 , 输出功率 3500W , 重量 95 公斤 , 尺寸 53*40*105 厘米 (OEM 定制/定制) ...)

其他参数 其他参数 其他参数 其他参数 其他参数

